




www.lexsolar.de/feedback

Layout diagram leXsolar-H₂ Ready-to-go 2.0
 Item-No.1219
 Bestückungsplan leXsolar-H₂ Ready-to-go 2.0
 Art.-Nr.1219




- | | |
|--|---|
| <p>1 1200-18 H2 Storage + 2optional expansions
1200-18 H2 Storage + 2optionale Erweiterung</p> <p>2 1100-31 Solar panel 2.5 V, 420 mA
1100-31 Solarmodul 2.5 V, 420 mA</p> <p>3 1200-17 H2 Charger
1200-17 H2 Charger</p> <p>4 1100-23 Potentiometer module
1100-23 Potentiometermodul</p> <p>5 1213-01 Gas storage module
1213-01 Gasspeichermodul</p> <p>6 1100-27 Motor module with
L2-02-017 Yellow propeller
1100-27 Motormodul ohne Getriebe mit
L2-02-017 Luftschraube (Propeller) gelb</p> | <p>7 1100-19 Base unit large
1100-19 Grundeinheit groß</p> <p>8 L2-06-132 Valve for H2 Storage
L2-06-132 Ventil für H2 Storage</p> <p>9 3x1218-02 PEM-Fuel cell module
3x1218-02 PEM-Brennstoffzellenmodul</p> <p>10 1218-03 Electrolyzer module 2.0
1218-03 Elektrolyseurmodul 2.0</p> |
|--|---|

Version number
 Versionsnummer

L3-03-163_28.04.2017

Layout diagram leXsolar-H₂ Ready-to-go 2.0
 Item-No.1219
 Bestückungsplan leXsolar-H₂ Ready-to-go 2.0
 Art.-Nr.1219



- 11 2xL2-06-011 Digital multimeter
2xL2-06-011 Digitalmultimeter
- 12 2xL2-06-012/013 Test lead black/red 25 cm
2xL2-06-012/013 Messleitung schwarz/rot 25 cm
- 13 L2-06-014/015 Test lead black/red 50 cm
L2-06-014/015 Messleitung schwarz/rot 50 cm
- 14 L2-04-022 Lamp with table clamp
L2-04-022 Lampe mit Tischklemme
- 15 1700-01 Ethanol fuel cell module
1700-01 Ethanol-Brennstoffzellenmodul